

Darkoo Optics (Zhongshan) Co., Ltd

## **Product Specification**

Product class: LED Lens

Item No.: DK-45-15-LENS-ST

Material: PMMA

Certification: RoHS

www.darkoo.cc Page 1 January 20,2015



## 中山市达尔科光学有限公司 Darkoo Optics (Zhongshan) Co., Ltd

#### Content

Specification	3
2D Drawing	4
Packing Details	5
Application Notes	F



Darkoo Optics (Zhongshan) Co., Ltd


### Specification

Item No	Picture	Size	Matched LED	Lighting Application
DK-45-15-LENS-ST	DARKCO	Diameter: Φ45mm Height: 23.4mm FWHM: 15°	XML	Stage lamp lens



Darkoo Optics (Zhongshan) Co., Ltd

### **Drawing**





### 中山市达尔科光学有限公司 Darkoo Optics (Zhongshan) Co., Ltd

### **Packing Details**

Packing Material	Packing Materil size	Packing Specification
Blister box	45-JC	
Pearl wool	315*230mm	96PCS/inner box
White paperboard	(400g) 310*235mm	4 inner box / 1 outer box
Inner box	335*245*105mm	
Outer box	A=B 510*330*255mm	

www.darkoo.cc Page 5 January 20,2015



Darkoo Optics (Zhongshan) Co., Ltd

### **Application Notes**

- (1) Please use a litter water and soft fabric (air-laid paper) to clean the lens & reflector if necessary.
  - (2) Forbid to use industrial solvent to clean the lens, such as alcohol.
- (3) The working temperature is -40°C  $\sim$  +80°C for lens, under 120°C for reflector.
- (4) Storage environment temperature is  $0^{\circ}\text{C} \sim 40^{\circ}\text{C}$ , humidity is  $30\% \sim 95\%$ . Optic Lens has the function to change the ray of light, it is made of optical material, the effect shall be influenced once pollute. Please do not open the packing before use it, to avoid the dust pollution.
- (5) Protect the product from the sun and other ultraviolet ray, as these will lead to aging, change color, crack, etc.
  - (6) Please ware gloves once install the lens, avoid to abrasion the lens surface.
- (7) Forbid to use acidic or alkaline solution touch the product, avoid to generate the chemical reactions.